



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUV21225 2-1/2 2/0-250MCM U Bolt Ground Clamp

*Abb Installation Products, Inc*

Catalog Number	GUV21225
Manufacturer	Abb Installation Products, Inc
Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250 Awg, Rod Size 2-1/2 to 2-7/8 Inches, Ips Pipe Size Max 2-1/2 Inches, Length 4-15/16 Inches, Width 4-3/16 Inches, Depth 1-9/16 Inches
Weight per unit	0.3310 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Conductor Size	2/0 AWG - 250kcmil
insulation	No

### Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

### Dimensions and Weight

Length	4-15/16 in
--------	------------

### Descriptions

Description	2-1/2 2/0-250MCM U BOLT GROUND CLAMP
extra long description	ABB GUV21225 U-BOLT GROUND CLAMP 25
Long Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250 AWG, Rod Size 2-1/2 to 2-7/8 Inches, IPS Pipe Size Max 2-1/2 Inches, Length 4-15/16 Inches, Width 4-3/16 Inches, Depth 1-9/16 Inches
Product Type	U-Bolt Ground Clamp 250-2/0
Special Features	Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area

### Manufacturer Information

Brand	Blackburn Grounding
GTIN	00783786803682
Manufacturers Part Number	GUV21225
UPC	783786803682

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
----------------------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	3
Package	30
Weight Per each	0.331

## Uses, Certifications, and Standards

standard	UL E3060, CSA 12798
----------	---------------------