



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GUV7821 7/8-1 Ground Clamp

Abb Installation Products, Inc

| | |
|------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | GUV7821 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Ground Clamp, 2-3/4 In Overall Length, Copper (Conductor) Material, 1-9/16 In Overall Width, 2-5/8 In Overall Height, 1 In (Maximum); 7/8 In (Minimum) Rod Size, 1 In (Maximum); 7/8 In (Minimum) Ips Size, #4 to #2/0 Awg Conductor Size, 0.68 LB |
| Weight per unit | 0.6840 (lbs/each) |
| Product Category | Ground Rods & Grounding System |

Features

| | |
|------------|----|
| insulation | No |
|------------|----|

Material, Color, and Finish

| | |
|--------------------|--------|
| Conductor Material | Copper |
|--------------------|--------|

Dimensions and Weight

| | |
|--------|----------|
| Length | 2-3/4 in |
|--------|----------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | 7/8-1 GROUND CLAMP |
| extra long description | ABB GUV7821 U BOLT GRD CLAMP COND R |

Manufacturer Information

| | |
|-------|---------------------|
| Brand | Blackburn Grounding |
| GTIN | 00783786803545 |
| UPC | 783786803545 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------------------------------------------------|
| Category Description | SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods |
| Type | GROUND CLAMP |

Packaging

| | |
|-----------------|-------|
| Carton | 25 |
| Weight Per each | 0.684 |

Uses, Certifications, and Standards

| | |
|----------|---------------------|
| standard | UL E3060, CSA 12798 |
|----------|---------------------|