

HALO®




H1499RT

4" Aperture
Shallow Ceiling
Remodel Housing
12V Low Voltage MR16
Halogen

RECESSED DOWNLIGHTING

- Thermally Protected Non-IC Shallow Ceiling Low Voltage Remodel Housing
- Integral magnetic Transformer
- Insulation must be kept 3" away from all sides of housing
- * For use with 12V MR16 halogen lamps

DIMENSIONS



DESCRIPTION

The H1499RT is a small aperture remodel housing for providing accent and task lighting. The H1499RT is designed for use in non-insulated existing ceiling or for existing insulated ceilings where insulation can be kept 3" from all sides of the housing. It can be installed from below the ceiling.

Housing

Die-stamped 20 gauge CRS with white powder coat finish.

Junction Box

J-Box features include:

- Listed for through branch circuit wiring
- Seven 1/2" trade size knockouts with true pry-out slots
- Four pryouts with integral strain relief for non-metallic sheathed cable

"Quick Connect" Connectors

Three "Quick Connect" connectors eliminate need for separate wire nuts - simply strip supply wires and push in

Socket

Ceramic socket with reflector for bi pin MR16 lamps .

Remodel Clips

Four remodel clips secure housing and accommodates 1/2" and 5/8" ceiling materials.

Transformer

120V magnetic transformer steps line voltage down to lamp operating voltage.

Support Spring

Support spring helps support weight of junction box and transformer. Automatically adjusts for different ceiling

materials..

Thermal Protector

Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation.

Labels

- UL/cUL Listed for Damp Location
- UL/cUL Listed for Feed Through

H1499IC

H1499T


H1499RT

H1499T75

1421 Reflector Trim

- Die cast trim ring with reflector cone
- Provides General Illumination
- Lamps:

H1499T	50W 12V MR16
H1499RT	
H1499IC	75W 12V MR16
H1499T75	



1421RG
White Trim, Residential Gold Reflector

1421CG
White Trim, Champagne Gold Reflector

1421C
White Trim, Clear Specular Reflector



1421SL
Silver Trim, Clear Specular Reflector

1421MB
White Trim, Black Specular Reflector

1421H
White Trim, Haze Reflector



1421BZ
Tuscan Bronze, Tuscan Bronze Reflector


1421AC
Antique Copper Trim, Antique Copper Reflector

1421SN
Satin Nickel Trim, Satin Nickel Reflector

1493 Coilex® Baffle

- Die cast trim ring
- Coilex® Baffle
- For general lighting
- Lamps:

H1499T	50W 12V MR16
H1499RT	
H1499IC	75W 12V MR16
H1499T75	



1493PB
Polished Brass Trim with Black Baffle

1493W
White with White Baffle

1493P
White with Black Baffle



1493SN
Satin Nickel Trim with Black Baffle

1493BC
Black Chrome Trim with Black Baffle

1493SL
Silver Trim with Black Baffle



1493TBZ
Tuscan Bronze Trim with Black Baffle

1493AC
Antique Copper Trim with Black Baffle

HALO®




H1499RT

4" Aperture
Shallow Ceiling
Remodel Housing
12V Low Voltage MR16
Halogen


RECESSED DOWNLIGHTING

- Thermally Protected Non-IC Shallow Ceiling Low Voltage Remodel Housing
- Integral magnetic Transformer
- Insulation must be kept 3" away from all sides of housing
- * For use with 12V MR16 halogen lamps

DIMENSIONS



Ceiling Opening should match template supplied with housing



DESCRIPTION

The H1499RT is a small aperture remodel housing for providing accent and task lighting. The H1499RT is designed for use in non-insulated existing ceiling or for existing insulated ceilings where insulation can be kept 3" from all sides of the housing. It can be installed from below the ceiling.

Housing

Die-stamped 20 gauge CRS with white powder coat finish.

Junction Box

J-Box features include:

- Listed for through branch circuit wiring
- Seven 1/2" trade size knockouts with true pry-out slots
- Four pryouts with integral strain relief for non-metallic sheathed cable

"Quick Connect" Connectors

Three "Quick Connect" connectors eliminate need for separate wire nuts - simply strip supply wires and push in

Socket

Ceramic socket with reflector for bi pin MR16 lamps .

Remodel Clips

Four remodel clips secure housing and accommodates 1/2" and 5/8" ceiling materials.

Transformer

120V magnetic transformer steps line voltage down to lamp operating voltage.

Support Spring

Support spring helps support weight of junction box and transformer. Automatically adjusts for different ceiling

materials..

Thermal Protector

Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping or misapplied insulation.

Labels

- UL/cUL Listed for Damp Location
- UL/cUL Listed for Feed Through

H1499IC

H1499T


H1499RT

H1499T75

1421 Reflector Trim

- Die cast trim ring with reflector cone
- Provides General Illumination
- Lamps:

H1499T	50W 12V MR16
H1499RT	
H1499IC	75W 12V MR16
H1499T75	



1421RG
White Trim, Residential Gold Reflector

1421CG
White Trim, Champagne Gold Reflector

1421C
White Trim, Clear Specular Reflector



1421SL
Silver Trim, Clear Specular Reflector

1421MB
White Trim, Black Specular Reflector

1421H
White Trim, Haze Reflector



1421BZ
Tuscan Bronze, Tuscan Bronze Reflector


1421AC
Antique Copper Trim, Antique Copper Reflector

1421SN
Satin Nickel Trim, Satin Nickel Reflector

1493 Coilex® Baffle

- Die cast trim ring
- Coilex® Baffle
- For general lighting
- Lamps:

H1499T	50W 12V MR16
H1499RT	
H1499IC	75W 12V MR16
H1499T75	



1493PB
Polished Brass Trim with Black Baffle

1493W
White with White Baffle

1493P
White with Black Baffle



1493SN
Satin Nickel Trim with Black Baffle

1493BC
Black Chrome Trim with Black Baffle

1493SL
Silver Trim with Black Baffle



1493TBZ
Tuscan Bronze Trim with Black Baffle

1493AC
Antique Copper Trim with Black Baffle