



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3942 Automation Way  
80525-0000, CO Fort Collins  
Phone: 970-305-3593  
Fax: 970-372-1731



## H457TATE010 4" Ic Rated Can

*Cooper Lighting Solutions*

Catalog Number	H457TATE010
Manufacturer	Cooper Lighting Solutions
Description	4" Led Housing Non-Ic, Air-Tite, 120V-277V, For Halo EL406, ELG406, ELSG406 Led Light Engines, 120V & 0-10VDC Dimmable
Weight per unit	3.6 (lbs/each)
Product Category	Led Recessed Architectural & S

### Features

amperage rating	0.121 A
Lamp Type	LED (Not Included)
Number of Lamps	1
Voltage Rating	120/277V

### Material, Color, and Finish

Style	(blank)
-------	---------

### Descriptions

Description	4" IC RATED CAN
extra long description	CLS H457TATE010 4" NON-IC NEW CONST
Long Description	4" LED Housing Non-IC, Air-Tite, 120V-277V, for Halo EL406, ELG406, ELSG406 LED Light Engines, 120V & 0-10VDC Dimmable
Product Type	4" Non-Ic New Construction Housing Unv
Special Features	Got Nail!™ bar hangers

### Manufacturer Information

Brand	HALO
GTIN	00080083692521
Manufacturers Part Number	H457TATE010
UPC	080083692521

### Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	4" H4 LED Housing

### Packaging

Carton	1
Weight Per each	3.62



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3942 Automation Way  
80525-0000, CO Fort Collins  
Phone: 970-305-3593  
Fax: 970-372-1731

## Uses, Certifications, and Standards

Application	lighting
Mounting	Recessed
standard	UL/cUL Listed - Damp Location;UL/cUL Listed - Wet Location;AIR-TITE (TM) Certified ASTM E283;Energy Star Certified;UL/cUL Listed 1598 Luminaire;IECC Compliant;California Title 24;RoHS Compliant;EMI/RFI per FCC 47CFR Part 18 Class B