



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2310ST LKG RCPT, 20A 125V, L5-20R, BK, Spring T *Hubbell Wiring Devices*

Catalog Number	HBL2310ST
Manufacturer	Hubbell Wiring Devices
Description	20A, 125V Edgeconnect™ Twist-Lock® Receptacle With Spring Termination
Weight per unit	0.1510 (lbs/each)
Product Category	Wiring Devices

Features

connection	Spring Termination
Dielectric Strength	Withstands 2,000V minimum
insulation	False
Material	Nylon
Number of Wires	3
pallet quantity	2250
Phase	1
Poles	2
Voltage Rating	125 V
Wattage	2,500
Wire Size	14 - 10 solid, 14 - 8 stranded (including compact stranded)

Dimensions and Weight

Size	3.28 in x 1.70 in x 1.47 in;Standard Sized Product
------	--

Descriptions

Description	LKG RCPT, 20A 125V, L5-20R, BK, SPRING T
extra long description	HWDK HBL2310ST LKG RCPT, 20A 125V,
Long Description	20A, 125V EdgeConnect™ Twist-Lock® Receptacle with Spring Termination
Product Type	LKG RCPT, 20A 125V, L5-20R, BK, Spring T
Special Features	Twist-Lock Receptacle with Spring Termination

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585569543
Manufacturers Part Number	HBL2310ST
UPC	783585569543

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
----------------------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.151

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L5-20R
standard	CSA Certified to Specification C22.2 No. 42;UL Listed To UL 498;WR Rating