



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL2315 LKG FLG-Inlt, 20A 125V, L5-20P, WH *Hubbell Wiring Devices*

Catalog Number	HBL2315
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 20A 125V Ac, 2-Pole 3-Wire Grounding, Nema L5-20P, Screw Terminal, Nylon Casing, Back Wired, White
Weight per unit	0.1320 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	20
connection	Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
insulation	Insulated Body
Material	Nylon
Number of Wires	3-Wire
pallet quantity	2160
Phase	1
Poles	2-Pole
Voltage Rating	125 VAC
Wattage	2,500
Wire Size	#16 to #8

### Dimensions and Weight

Size	2.88 in x 2.88 in x 2.09 in
------	-----------------------------

### Descriptions

Description	LKG FLG-INLT, 20A 125V, L5-20P, WH
extra long description	HWDK HBL2315 LKG FLG-INLT, 20A 125V
Long Description	Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 20A 125V AC, 2-Pole 3-Wire Grounding, NEMA L5-20P, Screw Terminal, Nylon casing, Back wired, White
Product Type	LKG FLG-Inlt, 20A 125V, L5-20P, WH
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585037783
Manufacturers Part Number	HBL2315
UPC	783585037783



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Flanged Inlet

## Packaging

Carton	1
Package	10
Weight Per each	0.132

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L5-20P
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498