### Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Insulgrip Connector

## HUBBELL

#### **Features**

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

#### **Ordering Information**

Description	Cord Diameter	UPC	Catalog Number
Black and white nylon	.230"720"(5.8-18.	783585174259	HBL5369C
	3)		

# 9 1 8

#### Listings


UL Listed to UL498 File E1706 CSA Certified to C22.2 No. 42 File 280 NEMA® WD-6 Compliant

#### **Specifications**


Housing/Cord Clamp Nylon
Contact Holder Nylon

Terminal Retainer
Contacts
Contacts
Contacts
Contacts
Contacts
Countacts
Cou

Terminal Clamp Nickel plated steel
Assembly Screws Nickel plated steel



ALL SCREWS PER
ARE COMBINATION
ROBERTSON/PHILLIPS/
SLOTTED HEAD



INSERT

CATALOG (NOT MA CAT. NO & HBL52

#### **Performance**

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #18-10 AWG copper conductors only

Terminal Identification Terminals identified in accordance with UL 498 and CSA

**Environmental** 

Flammability UL 94 HB or better

IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

#### **Accessories**

Weatherproof Boot HBL6018

#### Resources

Customer Use Drawing eCatalog

