



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5661 SGL RCPT, Ind GRD, 15A 250V, 6-15R, BR Hubbell Wiring Devices

Catalog Number	HBL5661
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack
Weight per unit	0.0680 (lbs/each)
Product Category	Wall Plates & Covers

Features

amperage rating	15
connection	Back and Side Wired
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	5500
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	3750
Wire Size	#12 to #10

Dimensions and Weight

Size	1.94 in x 1.63 in x 1.19 in
------	-----------------------------

Descriptions

Description	SGL RCPT, IND GRD, 15A 250V, 6-15R, BR
extra long description	HWDK HBL5661 SGL RCPT, IND GRD, 15A
Long Description	Straight Blade Devices, Receptacles, Single, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Brown, Single Pack
Product Type	SGL RCPT, Ind GRD, 15A 250V, 6-15R, BR
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013992
Manufacturers Part Number	HBL5661
series	Extra Heavy Duty
UPC	783585013992

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SINGLE RECEPTACLE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.068

Uses, Certifications, and Standards

Application	Extra Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	6-15R
standard	Certified to CSA 22.2, No. 42 File 285;Guide RTRT Fed Spec WC596G;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186