



MILBANK
ENERGY AT WORK



HC16146JIC12

Catalog Number	HC16146JIC12
Marketing Product Description	16x6x14 Hinge Cover Type 12 UL Listed Steel No Knockouts ANSI 61 Gray Continuous Hinge Clamps And Screws Gasket In Door Mounting Feet Welded Seams
UPC	784572112629
Length (IN)	6
Width (IN)	14
Height (IN)	16
Weight (LB)	22
Brand Name	Milbank
Type	Hinge Cover
Application	Enclosure for Mounting Electrical Equipment
Standard	UL Listed
Number Of Outlet	0
Material	Steel with Powder Coat Finish
Size	6L x 14W x 16H
Color	ANSI 61 Gray
Construction	Welded
Cable Entry	No Knockouts
Mounting	Wall Mount
NEMA Rating	Type 12

Hinge Type	Continuous Hinge with Removable Pin
Top	Plain Top
Door	1 Gasketed Door
Latch	Clamp and Screw on One Side
Support	Panel Supports

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.