



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353



## HRLED9030BK 5W BK 30K Led Puck / Button

Wac Lighting CO.,

Catalog Number	HRLED9030BK
Manufacturer	Wac Lighting CO.,
Description	The Edge-Lit Ledme Round Button Light Is Designed For Recessed or Surface Mounted Installations, Delivering Strong Evenly Distributed Light Output With The Latest In Led Technology. Class Ii, 24V Remote and Plug-In Transformers Allow Up to 12 Button Lights to Be Wired Together. Available With Black, White, or Brushed Nickel Finish. Includes 72" Of Wire, Button Lights Can Be Wired In A Series to One Another Up to The Maximum Load On The Power Supply Used.
Weight per unit	0.8800 (lbs/each)
Product Category	Lighting

### Features

bulb type	Module
Category	Specialty Items
Safety Rating	ETL, cETL
Voltage	24.00 IN

### Material, Color, and Finish

Finish	BLACK GLOSS
Style	Contemporary Modern

### Descriptions

Description	5W BK 30K LED PUCK / BUTTON
Long Description	The edge-lit LEDme Round Button Light is designed for recessed or surface mounted installations, delivering strong evenly distributed light output with the latest in LED technology. Class II, 24V remote and plug-in transformers allow up to 12 Button Lights to be wired together. Available with black, white, or brushed nickel finish. Includes 72" of wire, Button Lights can be wired in a series to one another up to the maximum load on the power supply used.
Product Type	Led Button Light

### Manufacturer Information

Brand	W.A.C. Lighting
GTIN	00790576345444
Manufacturers Part Number	HR-LED90-30-BK
UPC	790576345444



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive  
30336-0000, GA Atlanta  
Phone: 470-237-5352  
Fax: 470-237-5353

## Taxonomies, Classifications, and Categories

Category Description	DECORATIVE RESIDENTIAL
Type	Undercabinet

## Packaging

Carton	1
Weight Per each	0.88

## Uses, Certifications, and Standards

Energy Star	yes
-------------	-----