



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HUB400DN 4" Rigid Watertite D/C Hub

*Appleton/Oz Gedney*

|                  |   |
|------------------|---|
| Catalog Number   | HUB400DN  |
| Manufacturer     | Appleton/Oz Gedney  |
| Description      | Watertight Hub, 4 In Trade Size, Hub Model, Insulated, 1.06 In Thread Length, 5.75 In Hub Size, 1.56 In Length, 5.47 In Diameter, 4.63 In Knockout Size, 2.65 LB/Ea |
| Weight per unit  | 2.7 (lbs/each)  |
| Product Category | Rigid Conduit Fittings - Steel  |

### Features

|          |               |
|----------|---------------|
| Material | Zinc Die Cast |
|----------|---------------|

### Dimensions and Weight

|      |   |
|------|---|
| Size | 4 |
|------|---|

### Descriptions

|                        |                                    |
|------------------------|------------------------------------|
| Description            | 4" RIGID WATERTITE D/C HUB         |
| extra long description | EGS HUB400DN 4 ZDC WATER TIGHT HUB |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Appleton       |
| GTIN  | 00687855002207 |
| UPC   | 687855002207   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type                 | Watertight Hubs  |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 2    |
| Package         | 10   |
| Weight Per each | 2.65 |

### Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Application        | Used to Connect Rigid or IMC Conduit to a Threadless Opening in an Enclosure                          |
| standard           | UL Standard: 514B; UL Listed: E14814; CSA Standard: C22.2 No. 18.3; CSA Certified: 065178; NEMA: FB-1 |
| Temperature Rating | 105 Degree  |