



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPCS4040 4/0-2, 4/0-4 Insulation Piercing Connector

*Nsi Industries*

Catalog Number	IPCS4040
Manufacturer	Nsi Industries
Description	Nsi IPCS4040 Insulation Piercing CO
Weight per unit	0.4300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

amperage rating	405 (CU Amps) - 315 (AL Amps)
Conductor Size	4/0-2 AWG (Main)
Material	Fiber Reinforced Thermal Plastic
Tap Size	4/0-4 AWG
Voltage Rating	600 V

### Material, Color, and Finish

Color	Black
Finish	Thermal Plastic

### Dimensions and Weight

Size	L=3.50 - W=2.40 - H=3.30
------	--------------------------

### Descriptions

Description	4/0-2, 4/0-4 INSULATION PIERCING CONNECTOR
Long Description	NSI IPCS4040 Insulation Piercing Co
Product Type	Insulation Piercing Connector 4/0-4/0 Aw
Special Features	No need to strip wire - No tape or cover needed - Exclusive turbo spacer keeps tap side open while main conductor is being tightened

### Manufacturer Information

Brand	NSi
GTIN	00662381082664
Manufacturers Part Number	IPCS4040
UPC	662381082664

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Insulation Piercing Connectors

### Availability

Manufacturer Status	Inactive
Status	Inactive



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	4
Weight Per each	0.43

## Uses, Certifications, and Standards

Application	NSI
environmental conditions	90 C
Mounting	Clamp
standard	UL486B Listed
Temperature Rating	90 C