



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



IPCS4040 4/0-2, 4/0-4 Insulation Piercing Connector

Nsi Industries

Catalog Number	IPCS4040
Manufacturer	Nsi Industries
Description	Nsi IPCS4040 Insulation Piercing CO
Weight per unit	0.4300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

amperage rating	405 (CU Amps) - 315 (AL Amps)
Conductor Size	4/0-2 AWG (Main)
Material	Fiber Reinforced Thermal Plastic
Tap Size	4/0-4 AWG
Voltage Rating	600 V

Material, Color, and Finish

Color	Black
Finish	Thermal Plastic

Dimensions and Weight

Size	L=3.50 - W=2.40 - H=3.30
------	--------------------------

Descriptions

Description	4/0-2, 4/0-4 INSULATION PIERCING CONNECTOR
Long Description	NSI IPCS4040 Insulation Piercing Co
Product Type	Insulation Piercing Connector 4/0-4/0 Aw
Special Features	No need to strip wire - No tape or cover needed - Exclusive turbo spacer keeps tap side open while main conductor is being tightened

Manufacturer Information

Brand	NSi
GTIN	00662381082664
Manufacturers Part Number	IPCS4040
UPC	662381082664

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Insulation Piercing Connectors

Availability

Manufacturer Status	Inactive
Status	Inactive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298

Packaging

Carton	1
Package	4
Weight Per each	0.43

Uses, Certifications, and Standards

Application	NSI
environmental conditions	90 C
Mounting	Clamp
standard	UL486B Listed
Temperature Rating	90 C