



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISPBO20 14-2/0AWG 3PRT Tap Conn

*Nsi Industries*

Catalog Number	ISPBO20
Manufacturer	Nsi Industries
Description	The Polaris ISPBO2/0 Multi-Tap Direct Burial Submersible Offset Port Connector Features 3 Ports, Two On One Side and One On The Other, Sized For 2/0 - 14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Offset Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Meets or
Weight per unit	0.3100 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	3
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	2/0-14 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated

### Dimensions and Weight

Size	L=2.79 - W=4.18 - H=2.10
------	--------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	14-2/0AWG 3PRT TAP CONN
extra long description	NSI ISPBO2/0 POLARIS EDGE Connector
Features	The Polaris ISPBO2/0 3-Port Offset Entry Submersible Connector provides the simplest solution for forming a secure connection between up to three conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric
Long Description	The Polaris ISPBO2/0 Multi-Tap Direct Burial Submersible Offset Port Connector features 3 ports, two on one side and one on the other, sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each offset port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Installs with a hex key and torque wrench, without any tape or additional supplies. Meets or
Product Type	Polaris Edge Connector 2/0 Offset Epdm
Special Features	Offset 2/0-14 AWG - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381787873
Manufacturers Part Number	ISPBO2/0
UPC	662381787873

## Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Submersible Pedestal Connectors

## Packaging

Carton	3
Weight Per each	0.31

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1, UL486D
Temperature Rating	90 C