



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISR500 500MCM Polaris Insulated Butt SPLC

*Nsi Industries*

Catalog Number	ISR500
Manufacturer	Nsi Industries
Description	Insulated Butt Splice, #4 Awg Conductor Size, 500 MCM Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 4.62 In Overall Length, 600 V, 0.72 LB
Weight per unit	0.7200 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	500 MCM-4 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=4.620 - W=1.620 - H=3.000
------	-----------------------------

### Descriptions

Description	500MCM POLARIS INSULATED BUTT SPLC
extra long description	NSI ISR-500 POLARIS Ins Splice 500

### Manufacturer Information

GTIN	00662381951045
UPC	662381951045

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	IN-Line Splicer/Reducer

### Packaging

Carton	2
Weight Per each	0.72



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C