



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IT350C 350MCM-9AWG 2PRT, 2SIDE CLR Insld Tap Conn

*Nsi Industries*

Catalog Number	IT350C
Manufacturer	Nsi Industries
Description	The Polaris It-350C Multi-Tap Dual-Side Entry Vision Tap Connector Features 2 Ports Sized For 350 MCM to 6 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Dual Rated For Use With Copper or Aluminum Cables. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use
Weight per unit	0.3900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600
Warranty	1 YEAR
Wire Size	350 MCM-6 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Clear
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=2.470 - W=2.500 - H=2.440
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	350MCM-9AWG 2PRT,2SIDE CLR INSLTD TAP CONN
extra long description	NSI IT-350C POLARIS Vision Tap 2 Po
Features	The Polaris IT-350C 2-Port Dual-Side Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM to 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal conductor
Long Description	The Polaris IT-350C Multi-Tap Dual-Side Entry Vision Tap Connector features 2 ports sized for 350 MCM to 6 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Dual rated for use with copper or aluminum cables. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use
Product Type	Polaris Vision Tap 2 Port 350
Special Features	(2) 350 MCM-6 AWG - Dual Rated

## Manufacturer Information

Brand	Polaris
GTIN	00662381996527
Manufacturers Part Number	IT-350C
UPC	662381996527

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Double Sided Entry

## Packaging

Carton	4
Weight Per each	0.39

## Uses, Certifications, and Standards

Application	Wire Termination
Enclosure	Clear Plastisol
environmental conditions	Dry Location Only
standard	UL 486A/B
Temperature Rating	90