



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## K1W Wallplate PLST Des Horz 1DEV 1G W/Line W

*Pass & Seymour/Legrand*

Catalog Number	K1W
Manufacturer	Pass & Seymour/Legrand
Description	Constructed For Superior Resistance to Corrosion, This 1-Gang Wall Plate With One Horizontal Opening Is Recommended For Use In Food Processing Plants, Chemical Plants, and Other Industrial, Institutional, and Commercial Applications Where Corrosive Atmospheres Exist. This Wall Plate Can Be Customized With Over 300 Opening Styles.
Weight per unit	0.1462 (lbs/each)
Product Category	Wall Plates & Covers

### Features

cutout	For Use with Despard Devices
indoor/outdoor	Indoor
Mounting Type	Box Mounted
Number of Gangs	1
orientation	Vertical
Wall Plate Type	Despard

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Thickness	0.07
-----------	------

### Descriptions

Construction	Plastic
Description	WALLPLATE PLST DES HORZ 1DEV 1G W/LINE W
extra long description	P&S K1W PLATE PLST DES HORZ 1DEV 1G
Long Description	Constructed for superior resistance to corrosion, this 1-gang Wall Plate with one horizontal opening is recommended for use in food processing plants, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist. This Wall Plate can be customized with over 300 opening styles.
Product Type	Plate PLST Des Horz 1DEV 1G W/Line W

### Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007530032
Manufacturers Part Number	K1-W
UPC	785007530032



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	Wall Plate

## Packaging

Carton	1
Package	150
Weight Per each	0.1462

## Uses, Certifications, and Standards

standard	CSA, UL, CSA, UL514
----------	---------------------