



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

303 East Harned Avenue
74075-0000, OK Stillwater
Phone: 405-880-8633
Fax: 405-880-8634



L13.5T848GC840S 13.5W Led T8 48" 40K BLSTD 2100LM

Keystone Technologies

Catalog Number	L13.5T848GC840S
Manufacturer	Keystone Technologies
Description	13.5W, 2200 Lumen, 4', 220° Beam Angle, 4000K, Ballast Compatible, DLC 4.0, Coated
Weight per unit	0.0264 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	Ballast Dependent
ip rating	N/A
lumens	2200
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	13.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	4000
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	13.5W LED T8 48" 40K BLSTD 2100LM
extra long description	Key KT-LED13.5T8-48GC-840-S /G3 13.
Long Description	13.5W, 2200 Lumen, 4', 220° Beam Angle, 4000K, Ballast Compatible, DLC 4.0, Coated
Product Type	13.5W, 2200 Lumen, 4', 220° Beam Angle, 4000K, Ballast Compa

Manufacturer Information

Brand	Keystone
GTIN	00843654136387
Manufacturers Part Number	KT-LED13.5T8-48GC-840-S /G3
UPC	843654136387



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

303 East Harned Avenue
74075-0000, OK Stillwater
Phone: 405-880-8633
Fax: 405-880-8634

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
Weight Per each	0.0264

Uses, Certifications, and Standards

Energy Star	N
-------------	---