

Specifications



Eaton L1620PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 20A, Industrial, 480V, Back wiring, Yellow, Steel, Watertight, L16-20, Three-pole, Four-wire, Santoprene, 0.36 to 0.84 in, IP67

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking plug
CATALOG NUMBER	L1620PW
UPC	040893642062
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	1.025 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Watertight



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	20A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L16-20
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4 Grounding
TORQUE RATING	14-16 lbf-inch
VOLTAGE RATING	3Ø 480 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.36-0.84 in
DESIGN TYPE	Watertight locking plug
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Nylon
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight
TYPE	Locking plug

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 6
	NEMA 4
	NEMA 6P
	NEMA 4X
	IP67

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L1620PW
	Arrow Hart watertight locking plugs, connectors and receptacles spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton L1620PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 20A, Industrial, 480V, Back wiring, Yellow, Steel, Watertight, L16-20, Three-pole, Four-wire, Santoprene, 0.36 to 0.84 in, IP67

General specifications

PRODUCT NAME	Eaton Arrow Hart watertight locking plug
CATALOG NUMBER	L1620PW
UPC	040893642062
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	1.025 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Watertight



Powering Business Worldwide

Electrical Ratings

AMPERAGE RATING	20A
DEGREE OF PROTECTION	IP67
NEMA CONFIGURATION	L16-20
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4 Grounding
TORQUE RATING	14-16 lbf-inch
VOLTAGE RATING	3Ø 480 V

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.36-0.84 in
DESIGN TYPE	Watertight locking plug
DEVICE GRADE	Extra heavy-duty industrial specification grade
FACE/BODY MATERIAL	Nylon
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight
TYPE	Locking plug

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Environmental Specifications

ENVIRONMENTAL RESISTANCE	NEMA 6
	NEMA 4
	NEMA 6P
	NEMA 4X
	IP67

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Nickel plated brass

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L1620PW
	Arrow Hart watertight locking plugs, connectors and receptacles spec sheet



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

