



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L2N38 #2 3/8" 2 Hole Long Barrel Compression Lug

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | L2N38   |
| Manufacturer     | Nsi Industries  |
| Description      | 2 Hole Long Barrel Copper Compression Lug 2 Awg - 3/8" - 1" Mounting Spacing Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. Allows Easy Inspection Of The Termination to Assure Complete Cable Insertion. Tin-Plated to Provide Corrosion and Low Contact Resistance. Marked With Die Index and Color Coded. Listed For 35KV Maximum When Properly Installed. Rated 600V. Culus 486A/B Listed. UL467 Listed On Sizes 6 Awg - 3/0 Awg. Temperature Rating 90 Degrees C. |
| Weight per unit  | 0.0900 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                 |               |
|-----------------|---------------|
| Cable Size      | # 2 AWG (STR) |
| Material        | Copper        |
| Number of Holes | 2             |
| Stud Size       | 3/8           |
| Voltage Rating  | 600 V         |
| Warranty        | 1 YEAR        |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Brown      |
| Finish | Tin Plated |

### Dimensions and Weight

|      |                                     |
|------|-------------------------------------|
| Size | L=3.07 - W=.600 - OD=.420 - ID=.310 |
|------|-------------------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | #2 3/8" 2 HOLE LONG BARREL COMPRESSION LUG  |
| extra long description | NSI L2N-38 CU CMP Lug Long 2 AWG 3/   |
| Features               | 2 Hole Long Barrel Copper Compression Lug 2 AWG - 3/8" - 1" Mounting Spacing Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C. |
| Long Description       | 2 Hole Long Barrel Copper Compression Lug 2 AWG - 3/8" - 1" Mounting Spacing Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. Allows easy inspection of the termination to assure complete cable insertion. Tin-plated to provide corrosion and low contact resistance. Marked with die index and color coded. Listed for 35KV maximum when properly installed. Rated 600V. cULus 486A/B Listed. UL467 Listed on sizes 6 AWG - 3/0 AWG. Temperature rating 90 degrees C. |
| Product Type           | Cu CMP Lug Long 2 Awg 3/8 Bolt 1 Spac   |
| Special Features       | # 2 AWG (STR) - 3/8 Mounting Holes - 1 Hole Spacing   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381035059 |
| Manufacturers Part Number | L2N-38         |
| UPC                       | 662381035059   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Long Barrel - Two Hole            |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 50   |
| Weight Per each | 0.09 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C                                    |
| Mounting                 | 3/8 Mounting Holes                      |
| standard                 | UL486A/B, UL467 (8 AWG - 3/0 AWG)       |