



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L614 #6 1-Hole Long Barrel Compression Lug 1/4" Bolt

Nsi Industries

| | |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | L614 |
| Manufacturer | Nsi Industries |
| Description | Compression Lug, #8 Awg Conductor Size, #6 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Blue Insulation Color, 1 Conductor, +90 °C Operating Temperature, 1.772 In Overall Length, 600 V, 0.02 LB/Ea |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|---------------|
| Cable Size | # 6 AWG (STR) |
| Material | Copper |
| Number of Holes | 1 |
| Stud Size | 1/4 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|-------|------|
| Color | Blue |
|-------|------|

Dimensions and Weight

| | |
|------|-------------------------------------|
| Size | L=1.77 - W=.420 - OD=.300 - ID=.200 |
|------|-------------------------------------|

Descriptions

| | |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | #6 1-HOLE LONG BARREL COMPRESSION LUG 1/4" BOLT |
| extra long description | NSI L614 CU CMP Lug Long 6 AWG 1/4 |
| Features | 1 Hole Long Barrel Copper Compression Lug 6 AWG - 1/4" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. . |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381034007 |
| UPC | 662381034007 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Long Barrel - One Hole |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.02 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------------------|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| Mounting | 1/4 Mounting Hole |
| standard | UL486A/B, UL467 (8 AWG -3/0 AWG) |