



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive
71730-0000, AR El Dorado
Phone: 870-639-6289
Fax: 870-864-8850



L838P #8, 3/8STD 1H CMP Lug

Nsi Industries

Catalog Number	L838P
Manufacturer	Nsi Industries
Description	1 Hole Long Barrel Copper Compression Lug With Peep Hole 8 Awg - 3/8" Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Low Contact Resistance. Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed and to Cable Manufacturer Instructions. Temperature Rating 90 Degrees C.
Weight per unit	2.2 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Cable Size	# 8 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Red
Finish	Tin Plated

Dimensions and Weight

Size	L=1.52 - W=.420 - OD=.295 - ID=.205
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive
71730-0000, AR El Dorado
Phone: 870-639-6289
Fax: 870-864-8850

Descriptions

Description	#8,3/8STD 1H CMP LUG
extra long description	NSI L838P CU CMP Lug Long 8 AWG 3/8
Features	1 Hole Long Barrel Copper Compression Lug with Peep Hole 8 AWG - 3/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Long Description	1 Hole Long Barrel Copper Compression Lug with Peep Hole 8 AWG - 3/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Product Type	Cu CMP Lug Long 8 Awg 3/8 Bolt Size-Peep
Special Features	# 8 AWG (STR) - 3/8 Mounting Hole

Manufacturer Information

Brand	NSi
GTIN	00662381336309
Manufacturers Part Number	L838P
UPC	662381336309

Taxonomies, Classifications, and Categories

Category Description	T&B C TAP LUGS
Type	Long Barrel - One Hole With Peep Hole

Packaging

Carton	1
Weight Per each	2.2

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)