



Item #	Description	Voltage	Watt	Incandescent Wattage Comparison	Lumens	LPW	CCT	CRI	M.O.L. (inches)	Diameter (inches)	Case Quantity	Enclosed/ Recessed Luminaire	Energy Star® Rated	Replaces
--------	-------------	---------	------	---------------------------------------	--------	-----	-----	-----	--------------------	----------------------	------------------	------------------------------------	--------------------------	----------

40W Equivalent Options

6W A19 A-Lamp - DIMMABLE - 25,000 Hours Rated Life

L6A19D2524K	6W Dimmable A-Lamp - 2400K	120	6	40	375	62.5	2400K	80	4.0	2.2	12	Y	N	LED7A19D0D24K LED7A19D24K
L6A19D2550K	6W Dimmable A-Lamp - 5000K	120	6	40	525	87.5	5000K	80	4.0	2.2	12	Y	Y	LED7A19D0D50K LED7A19D50K

6W A19 A-Lamp - Non Dimmable - 15,000 Hours Rated Life

L6A19N1530K	6W Non Dimmable A-Lamp - 3000K	120	6	40	480	80.0	3000K	80	4.0	2.2	12	Y	Y	LED5A1930K
L6A19N1541K	6W Non Dimmable A-Lamp - 4100K	120	6	40	500	83.3	4100K	80	4.0	2.2	12	Y	Y	LED5A1941K
L6A19N1550K	6W Non Dimmable A-Lamp - 5000K	120	6	40	525	87.5	5000K	80	4.0	2.2	12	Y	Y	LED5A1950K

60W Equivalent Options

9W A19 A-Lamp - DIMMABLE - 25,000 Hours Rated Life

L9A19D2527K	9W Dimmable A-Lamp - 2700K	120	9	60	800	88.9	2700K	80	4.3	2.4	12	Y	Y	LED10A19D0D27K LED10A19D27K
L9A19D2530K	9W Dimmable A-Lamp - 3000K	120	9	60	825	91.7	3000K	80	4.3	2.4	12	Y	Y	LED10A19D0D30K LED10A19D30K
L9A19D2541K	9W Dimmable A-Lamp - 4100K	120	9	60	850	94.4	4100K	80	4.3	2.4	12	Y	Y	LED10A19D0D41K LED10A19D41K

9W A19 A-Lamp - DIMMABLE - 15,000 Hours Rated Life

L9A19D1527K24	9W Dimmable A-Lamp - 2700K 24PK	120	9	60	800	88.9	2700K	80	4.3	2.4	2	Y	Y	
L9A19D1527K	9W Dimmable A-Lamp - 2700K	120	9	60	800	88.9	2700K	80	4.3	2.4	12	Y	Y	LED9A19D27K
L9A19D1530K	9W Dimmable A-Lamp - 3000K	120	9	60	825	91.7	3000K	80	4.3	2.4	12	Y	Y	LED9A19D30K
L9A19D1541K	9W Dimmable A-Lamp - 4100K	120	9	60	850	94.4	4100K	80	4.3	2.4	12	Y	Y	LED9A19D41K
L9A19D1550K	9W Dimmable A-Lamp - 5000K	120	9	60	850	94.4	5000K	80	4.3	2.4	12	Y	Y	LED9A19D50K

9W A19 A-Lamp - Non Dimmable - 15,000 Hours Rated Life

L9A19N1527K	9W Non Dimmable A-Lamp - 2700K	120	9	60	800	88.9	2700K	80	4.4	2.4	12	Y	Y	LED10A19D0D27K LED9A1927K
L9A19N1530K	9W Non Dimmable A-Lamp - 3000K	120	9	60	825	91.7	3000K	80	4.4	2.4	12	Y	Y	LED10A19D0D30K LED9A1930K
L9A19N1541K	9W Non Dimmable A-Lamp - 4100K	120	9	60	850	94.4	4100K	80	4.4	2.4	12	Y	Y	LED10A19D0D41K LED9A1941K
L9A19N1550K	9W Non Dimmable A-Lamp - 5000K	120	9	60	875	97.2	5000K	80	4.4	2.4	12	Y	Y	LED10A19D0D50K LED9A1950K

75W Equivalent Options

11W A19 A-Lamp - DIMMABLE - 25,000 Hours Rated Life

L11A19D2527K	11W Dimmable A-Lamp - 2700K	120	11	75	1150	104.5	2700K	80	4.6	2.4	12	Y	Y	LED13A21D0D27K
--------------	-----------------------------	-----	----	----	------	-------	-------	----	-----	-----	----	---	---	----------------

11W A19 A-Lamp - Non Dimmable - 15,000 Hours Rated Life

L11A19N1527K	11W Non Dimmable A-Lamp - 2700K	120	11	75	1100	100.0	2700K	80	4.6	2.4	12	Y	Y	LED13A2127K
L11A19N1530K	11W Non Dimmable A-Lamp - 3000K	120	11	75	1150	104.5	3000K	80	4.6	2.4	12	Y	Y	LED13A2130K
L11A19N1550K	11W Non Dimmable A-Lamp -5000K	120	11	75	1225	111.4	5000K	80	4.6	2.4	12	Y	Y	LED13A2150K

continued next page

WARRANTIES and CERTIFICATIONS

5 YEAR WARRANTY*
25,000 Hour Lamps

3 YEAR WARRANTY*
15,000 Hour Lamps

*Based on 12 hours use per day



L6A19D25

L6A19N15

L9A19D25
L9A19D15

L9A19N15

L11A19D25

L11A19N15

L16A19N15
L15A19D25

Specification Notes:

All Energy Star rated products meet the new Energy Star 2.0 spec for light distribution

Vapor tight or jelly jar applications may reduce life

For the most up-to-date specs, please visit www.tcpi.com





Item #	Description	Voltage	Watt	Incandescent Wattage Comparison	Lumens	LPW	CCT	CRI	M.O.L. (inches)	Diameter (inches)	Case Quantity	Enclosed/ Recessed Luminaire	Energy Star® Rated	Replaces
--------	-------------	---------	------	---------------------------------------	--------	-----	-----	-----	--------------------	----------------------	------------------	------------------------------------	--------------------------	----------

★ SEE NEW 100W EQUIVALENT SPEC SHEET ★

100W Equivalent Options

16W A19 A-Lamp - Non Dimmable - 15,000 Hours Rated Life

L16A19N1527K	16W Non Dimmable A-Lamp - 2700K	120	16	100	1600	100.0	2700K	80	4.6	2.5	12	Y	Y	LED15A2127K
L16A19N1530K	16W Non Dimmable A-Lamp - 3000K	120	16	100	1625	101.6	3000K	80	4.6	2.5	12	Y	Y	LED15A2130K
L16A19N1541K	16W Non Dimmable A-Lamp - 4100K	120	16	100	1650	103.1	4100K	80	4.6	2.5	12	Y	Y	LED15A2141K
L16A19N1550K	16W Non Dimmable A-Lamp - 5000K	120	16	100	1675	104.7	5000K	80	4.6	2.5	12	Y	Y	LED15A2150K

15W A19 A-Lamp - DIMMABLE - 25,000 Hours Rated Life

L15A19D2527K	15W Dimmable A-Lamp - 2700K	120	15	100	1600	106.7	2700K	80	4.6	2.5	12	Y	Y	LED18A21D0D27K LED16A21D27K
L15A19D2530K	15W Dimmable A-Lamp - 3000K	120	15	100	1625	108.3	3000K	80	4.6	2.5	12	Y	Y	LED18A21D0D30K LED16A21D30K
L15A19D2541K	15W Dimmable A-Lamp - 4100K	120	15	100	1650	110.0	4100K	80	4.6	2.5	12	Y	Y	LED18A21D0D41K LED16A21D41K
L15A19D2550K	15W Dimmable A-Lamp - 5000K	120	15	100	1675	111.7	5000K	80	4.6	2.5	12	Y	Y	LED18A21D0D50K LED16A21D50K

WARRANTIES and CERTIFICATIONS

5 YEAR WARRANTY*
25,000 Hour Lamps

3 YEAR WARRANTY*
15,000 Hour Lamps

*Based on 12 hours use per day



L6A19D25 L6A19N15 L9A19D25
L9A19D15 L9A19N15 L11A19D25 L11A19N15 L16A19N15
L15A19D25

Specification Notes:

All Energy Star rated products meet the new Energy Star 2.0 spec for light distribution

Vapor tight or jelly jar applications may reduce life

For the most up-to-date specs, please visit www.tcpi.com

