



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LC1420CI 1-F20T12PH 118V Bal *Advance By Signify*

Catalog Number	LC1420CI
Manufacturer	Advance By Signify
Description	00781087101308 0781087 781087101308 78108710130 10130 LC1420 Ballast (1)F20T12 PH 120V Advance Ballast LC1420CI Advance Ballast LC1420CI Signifi Electronics LC1420C1 Signifi Electronics LC1420CI Signify Electronics LC1420C1 Signify Electronics LC1420CI Signify LC1420C1 Signify LC1420CI 20332939
Weight per unit	0.7400 (lbs/each)
Product Category	Magnetic Linear Fluorescent Ba

### Features

Ballast Factor	0.93
Lamp Type	T12
Number of Lamps	1
Power Factor	NORMAL
start type	PREHEAT
total harmonic distortion	10
Voltage Rating	120
Wattage	20
Wire Type	SOLID

### Material, Color, and Finish

Housing Material	Metal
------------------	-------

### Descriptions

Description	1-F20T12PH 118V BAL
extra long description	ADV LC1420CI MAG BALLAST (1)F20T12
Long Description	00781087101308 0781087 781087101308 78108710130 10130 LC1420 BALLAST (1)F20T12 PH 120V Advance Ballast LC1420CI Advance Ballast LC1420CI Signifi Electronics LC1420C1 Signifi Electronics LC1420CI Signify Electronics LC1420C1 Signify Electronics LC1420CI Signify LC1420C1 Signify LC1420CI 20332939
Product Type	Mag Ballast (1)F20T12 PH 120V
Special Features	UL, CSA, RoHS

### Manufacturer Information

Brand	Advance
GTIN	00781087101308
Manufacturers Part Number	LC1420CI
UPC	781087101308



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Magnetic Fluorescent

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Package	12
Weight Per each	0.74

## Uses, Certifications, and Standards

Application	L(2.860) x W(0.960) x H(1.000)
Frequency Rating	60