



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LCC638DL 6AWG 2HOLE Lug Panduit Corporation

|                  |   |
|------------------|---|
| Catalog Number   | LCC638DL  |
| Manufacturer     | Panduit Corporation   |
| Description      | Long Barrel Lug, #6 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Blue (Code) Insulation Color, +90 °C Operating Temperature, 3.15 In Overall Length, 35 KV, 0.0344 LB/Ea |
| Weight per unit  | 0.0344 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                 |                   |
|-----------------|-------------------|
| Material        | Tin-Plated Copper |
| media           | Yes               |
| Number of Holes | 2                 |
| Stud Size       | 3/8               |

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Blue |
|-------|------|

### Dimensions and Weight

|      |             |
|------|-------------|
| Size | #6 AWG Code |
|------|-------------|

### Descriptions

|                        |                                    |
|------------------------|------------------------------------|
| Description            | 6AWG 2HOLE LUG                     |
| extra long description | PAN LCC6-38D-L Pan-Lug™ LCC6-38D-L |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983382590 |
| UPC   | 074983382590   |

### Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Compression Lug                   |

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 50     |
| Weight Per each | 0.0344 |

### Uses, Certifications, and Standards

|          |  |
|----------|--|
| Mounting | 1-1/8  |
| standard | CSA certified C22.2 No. 65-13, UL Listed to 486A-486B File #E52164, ABS approved, NEBS Level 3 |