



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7T824GC850D 7W Led T8 24" 50K Single End Line Voltage *Keystone Technologies*

| | |
|------------------|--|
| Catalog Number | LED7T824GC850D |
| Manufacturer | Keystone Technologies |
| Description | 7W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 2, 5000K, Direct Drive |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 1000 |
| Nominal Length | 24 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 7 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 5000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|--|
| Construction | Frosted Shatterproof Glass |
| Description | 7W LED T8 24" 50K SINGLE END LINE VOLTAGE |
| extra long description | Key KT-LED7T8-24GC-850-D-CP 7W, 100 |
| Long Description | 7W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 2, 5000K, DIRECT DRIVE |
| Product Type | 7W, 1000 Lumen, 2', 240' Beam Angle, Ballast Bypass, DLC 4.0 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Keystone |
| GTIN | 00890949013212 |
| Manufacturers Part Number | KT-LED7T8-24GC-850-D-CP |
| UPC | 890949013212 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|-----|
| Carton | 25 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|