



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED82PH840D 8W Led 2PIN CFL 40K Horizontal Ballast Bypass

Keystone Technologies

Catalog Number	LED82PH840D
Manufacturer	Keystone Technologies
Description	8W 2-Pin Compact Led Lamp, Horizontal Orientation, 120-277V Input, G24D Base, 4000K
Weight per unit	0.2600 (lbs/each)
Product Category	Integrated Lamps

Features

Ballast Type	N/A
beam angle	120
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	900;900
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	8
Wire Type	N/A

Material, Color, and Finish

Base Type	G24d
color rendering index (cri)	80-89
color temperature	4000;4000
housing color	N/A

Descriptions

Construction	N/A
Description	8W LED 2PIN CFL 40K HORIZONTAL BALLAST BYPASS
extra long description	Key KT-LED82P-H-840-D-DP 8W , 1000
Long Description	8W 2-PIN COMPACT LED LAMP, HORIZONTAL ORIENTATION, 120-277V INPUT, G24D BASE, 4000K
Product Type	8W , 1000 Lumen, Horizontal, G24D, Bypass 2 Pin & 4 Pin Ball

Manufacturer Information

Brand	Keystone
GTIN	00890949012727
Manufacturers Part Number	KT-LED82P-H-840-D /G2
UPC	890949012727



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED PLUG-IN (REPLACEMENT FOR CFL BIAX LAMPS)

Packaging

Carton 1

Package 50

Weight Per each 0.26

Uses, Certifications, and Standards

Energy Star N