



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## LS7.9520A 20.5" Unctd SS Cable Tie

*Abb Installation Products, Inc*

Catalog Number	LS7.9520A
Manufacturer	Abb Installation Products, Inc
Description	Ball-Lock 304 Stainless Steel Cable Tie, Uncoated, For Temperatures Up to 300 Degrees Celsius (572 F) For Indoor and Outdoor Applications, Suitable For High Temperature Environments, UI/En/CSA62275 Type 2S Rated For Ah-1 Plenum, Length Of 520MM (20.5 Inches), Width Of 7.75MM (0.305 Inches), Thickness Of 0.25MM (0.01 Inches), Tensile Strength Rating Of 2002 Newtons (450 Pounds)
Weight per unit	0.0200 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Tensile Strength	450;2002
------------------	----------

### Dimensions and Weight

Length	20.5
Thickness	0.01
Width	0.305

### Descriptions

Description	20.5" UNCTD SS CABLE TIE
extra long description	ABB LS-7.9-520A CABLE TIE 302/304 S
Long Description	Ball-Lock 304 Stainless Steel Cable Tie, Uncoated, for Temperatures up to 300 Degrees Celsius (572 F) for Indoor and Outdoor Applications, Suitable for High Temperature Environments, UL/EN/CSA62275 Type 2S Rated for AH-1 Plenum, Length of 520mm (20.5 Inches), Width of 7.75mm (0.305 inches), Thickness of 0.25mm (0.01 Inches), Tensile Strength Rating of 2002 Newtons (450 Pounds)
Product Type	Cable Tie 302/304 SST 450LB 21 Bal

### Manufacturer Information

Brand	Ty-Rap
GTIN	00786210242224
Manufacturers Part Number	LS-7.9-520A
UPC	786210242224

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Stainless Steel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty ..... 50 .....

## Packaging

Carton ..... 50 .....

Weight Per each ..... 0.02 .....

## Uses, Certifications, and Standards

standard ..... UL E49405 .....