



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LT34500 3/4" Met L/T, Non UI 500' *Southwire Company*

Catalog Number	LT34500
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 3/4 In Trade Size, 1.03 to 1.05 In Conduit Outer Diameter, 0.82 to 0.84 In Conduit Inner Diameter, Titan(R) Ef Style, 500 FT Length, Galvanized, Gray, 5 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 29 LB/100 FT
Weight per unit	0.2700 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1035
------------------	------

Descriptions

Description	3/4" MET L/T, NON UL 500'
extra long description	SWC 55094005 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886053276
UPC	032886053276

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	500
Weight Per each	0.27