



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LTC075 3/4" PVC Smooth NM LT Conduit

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | LTC075 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved For Outdoor and Direct Burial In The Us, UI Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, Csa Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black With Orange Markings |
| Weight per unit | 0.2160 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|------------------|---------|
| Inside Diameter | 0.81890 |
| outside diameter | 1.05120 |
| Voltage Rating | 600 V |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|--------|---------|
| Length | 1.20080 |
|--------|---------|

Descriptions

| | |
|------------------------|---|
| Also Known As... | Liquid Tight Conduit Carflex® |
| Description | 3/4" PVC SMOOTH NM LT CONDUIT |
| extra long description | ABB LTC075 3/4IN LT TYPE B COND PVC |
| Long Description | Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 3/4 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings |
| Product Type | 3/4IN LT Type B Cond PVC BLK |
| similar brands | Sealtite® |
| Special Features | The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-----------------|
| Brand | T&B Ind Fitting |
| GTIN | 00786210789552 |
| Manufacturers Part Number | LTC075 |
| UPC | 786210789552 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NON-METALLIC SEALTITE AND FITTINGS |
| Type | Liquidtight Flexible Non-Metallic Conduit |

Trade Size

| | |
|------------|--------|
| Trade Size | 3/4 in |
|------------|--------|

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Weight Per foot | 0.216 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles |
| standard | UL E95745, CSA |