



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU50MED 50W E17 High Pressure Sodium Clear Med Base Lamp

Sylvania-Ledvance

| | |
|------------------|---|
| Catalog Number | LU50MED |
| Manufacturer | Sylvania-Ledvance |
| Description | 50W Lumalux High Pressure Sodium Hid Lamp, E26 Based, ED17 Bulb, Universal Burn, Clear, 1900K |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Hid High Pressure Sodium Lamps |

Features

| | |
|----------------|----------------------|
| average life | 24000 |
| Base | E26 Medium |
| Fixture Type | Open |
| Lamp Type | HIGH PRESSURE SODIUM |
| lumens | 4000 |
| Shape | E17 |
| Voltage Rating | 52 |
| Wattage | 50 |

Material, Color, and Finish

| | |
|-----------------------------|-------|
| color rendering index (cri) | 21 |
| color temperature | 1900 |
| Finish | Clear |

Dimensions and Weight

| | |
|------|------|
| Size | 5.43 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 50W E17 HIGH PRESSURE SODIUM CLEAR MED BASE LAMP |
| extra long description | SYL LU50/MED/67502 LU50MED 20/CS 1/ |
| Long Description | 50W LUMALUX high pressure sodium HID lamp, E26 based, ED17 bulb, universal burn, clear, 1900K |
| Product Type | LU50MED 20/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | SYLVANIA |
| GTIN | 00046135675027 |
| Manufacturers Part Number | LU50/MED/67502 |
| UPC | 046135675027 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------|
| Category Description | SODIUM |
| Type | High Intensity Discharge (HID) |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 20 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|----------|-----|
| standard | S68 |
|----------|-----|