

## Magnetic Ballast



ORDERING INFORMATION						
Lamps per Ballast	Lamp Watts	Catalog #	Voltage	Current (lamps)	Input watts	Ballast Factor
<b>F40T12, F4T12/U, 460 MA F40T12/ES, F40T12/U/ES 430 MA</b>						
1	40/34	M1/40RS-120	120	0.43/0.37	51/44	95% 88%
1	40/34	M1/40RS-277	277	0.19/0.17	52/46	95% 88%
2	40/34	M2/40RS-120	120	0.74/0.63	87/74	92% 88%
2	40/34	M2/40RS-277	277	0.32/0.28	87/77	93% 88%
<b>F96T12 425 MA</b>						
1	75	M1/75IS-120	120	0.83	93	76%
1	75	M1/75IS-277	277	0.36	92	76%
2	75	M2/75IS-120	120	1.35	156	76%
2	75	M2/75IS-277	277	0.63	156	80%
<b>F96T12/HO 800MA F912/HO/ES</b>						
1	110/95	M1/110RS-120	120	1.38/1.20	153/128	102% 95%
1	110/95	M1/110RS-277	277	0.57/0.50	147/123	99% 92%
2	110/95	M2/110RS-120	120	2.19/1.92	244/218	95% 94%
2	110/95	M2/110RS-277	277	0.94/0.78	244/209	95% 90%

## Electronic Ballast



ORDERING INFORMATION						
Lamps per Ballast	Description	ANSI 120V	Input Watts 277V	Ballast 120V	Factor 277V	Quantity
1	EP1/312S/120-277SC	32	32	0.87	0.87	10
2 or 1	EP2/312S/120-277SC	59	58	0.87	0.87	10
3 or 2	EP3/312S/120-277SC	88	85	0.87	0.87	10
4 or 3	EP4/312S/120-277SC	115	112	0.87	0.87	10