



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MAL3L3WH Maestro 300W/300W White Lutron

Catalog Number	MAL3L3WH
Manufacturer	Lutron
Description	Maestro Dual Incandescent/Halogen Dimmer, Single-Pole, 120V/300W Each Dimmer In White
Weight per unit	0.3500 (lbs/each)
Product Category	Lighting Dimmers

Features

actuator	Tapswitch
connection	Screw Terminal
Connection Type	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
media	Yes
Poles	1
Switch Type	Tapswitch
Voltage Rating	120
Wattage	300

Material, Color, and Finish

Color	White
Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

Descriptions

Description	MAESTRO 300W/300W WHITE
extra long description	LUT MA-L3L3-WH MA DIM/DIM 300W/300W
Long Description	Maestro Dual Incandescent/Halogen Dimmer, Single-pole, 120V/300W each dimmer in white
Product Type	Ma Dim/Dim 300W/300W WH
Special Features	Controls 300 W incandescent or halogen loads. Dimmers (top/bottom). Replacement for stacked switches. Tap on to preset light level;tap off. Tap twice for full on. Touch rocker to adjust light level. Single location only. Dimmer advanced programming features available.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lutron
GTIN	00027557411370
Manufacturers Part Number	MA-L3L3-WH
UPC	027557411370

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dual digital-face dimmer (two loads), single-pole

Availability

Status	Inactive
--------	----------

Packaging

Carton	24
Package	48
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing
Frequency Rating	50 to 60
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL