



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road
78238-0000, TX Leon Valley
Phone: 210-522-0146
Fax: 210-522-0732



MC143WG 14/3 WG MC Sol BK/RD/WH Alu Armor 250'

Southwire Company

Catalog Number	MC143WG
Manufacturer	Southwire Company
Description	14-3 Solid Black, Red, White, Green - MC Tuff®, Blue Interlocked Lightweight Galvanized Steel Armor With Phase Id - Type MC - 250' Coil
Weight per unit	0.1050 (lbs/each)
Product Category	Teck

Features

Bend Radius	7.515
Conductor Size	14 AWG Conductor And Ground
gauge	14 AWG
Inside Diameter	0.301
Material	Galvanized Steel
Number of Conductors	4
outside diameter	0.501
Voltage Rating	600V

Material, Color, and Finish

Conductor Material	Copper
Finish	Blue Paint
Insulation Material	THHN

Dimensions and Weight

Length	3000
--------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road
78238-0000, TX Leon Valley
Phone: 210-522-0146
Fax: 210-522-0732

Descriptions

extra long description

Features

AFC 1702B42T00 14-3 MCS 250C

Long Description

MC Tuff is a lightweight, high-strength Type MC Cable with blue galvanized steel interlocked armor that features ColorSpec®ID/ColorTrak® ID for easy identification. MC Tuff cables meet UL Standard 1569 and NEC 330, have no conductor count limit, and offer various conductor bundle combinations. These bundles consist of THHN/THWN rated conductors that are twisted and wrapped with polypropylene assembly tape. They also come with an insulated green equipment grounding conductor. Additionally, Atkore offers a G

Product Type

14-3 Solid Black, Red, White, Green - MC Tuff®, Blue Interlocked Lightweight Galvanized Steel Armor with phase ID - Type MC - 250' Coil

Short Description

14-3 MCS 250C

Special Features

Cable tray rated, install per NEC; May be surfaced mounted and embedded in plaster; Environmental air-handling space installation per NEC 300.22; UL Class?ed 1, 2, and 3 hour through (Fire) penetration product, R-14141; Made in USA of US and/or imported materials; ColorSpec ID system

Manufacturer Information

Brand

Flexible Conduit

GTIN

00077680195265

Manufacturers Part Number

1702B42T00

UPC

077680195265

Taxonomies, Classifications, and Categories

Category Description

BX & MC

Type

Traditional Lightweight Type MC Cable With Ground And Neutral

Trade Size

Trade Size

14-3

Availability

Status

Inactive

Packaging

Carton

250

Weight

686.4

Weight Per each

0.105



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5300 Bandera Road
78238-0000, TX Leon Valley
Phone: 210-522-0146
Fax: 210-522-0732

Uses, Certifications, and Standards

standard

UL 83, 1479, 1569, 1581, 2556 File Number E80042, UL File Number R-14141, NEC 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, Federal Specification A-A-59544 (Formerly J-C-30B), Meets OSHA And HUD Requirements, ISO 9001 Certified

Temperature Rating

194