



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MCT102SLBKWH250 MC 10/2 SL BK/WH 250'

Afc Cable

Catalog Number	MCT102SLBKWH250
Manufacturer	Afc Cable
Description	MC Cable, Black;White, Made In Usa, 2 - Conductors, 250 FT Overall Length, Carton Package Type, Solid Solid/Strand, 0.222 LB (Feet) Weight
Weight per unit	0.2220 (lbs/each)
Product Category	Armored Cable - BX - Ac - MC

Features

Bend Radius	8.73
Conductor Size	10 AWG Conductor And Ground
gauge	10 AWG
Inside Diameter	0.382
Material	Galvanized Steel
outside diameter	0.582
Voltage Rating	600V

Material, Color, and Finish

Conductor Material	Copper
Finish	Blue Paint
Insulation Material	THHN

Dimensions and Weight

Length	3000
--------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	MC 10/2 SL BK/WH 250'
extra long description	AFC 1707B42T00 10-2 MCS 250C
Features	MC Tuff is a lightweight, high-strength Type MC Cable with blue galvanized steel interlocked armor that features ColorSpec®ID/ColorTrak® ID for easy identification. MC Tuff cables meet UL Standard 1569 and NEC 330, have no conductor count limit, and offer various conductor bundle combinations. These bundles consist of THHN/THWN rated conductors that are twisted and wrapped with polypropylene assembly tape. They also come with an insulated green equipment grounding conductor. Additionally, Atkore offers a G
Special Features	Cable tray rated, install per NEC; May be surfaced mounted and embedded in plaster; Environmental air-handling space installation per NEC 300.22; UL Classified 1, 2, and 3 hour through (Fire) penetration product, R-14141; Made in USA of US and/or imported materials; ColorSpec ID system

Manufacturer Information

Brand	AFC CABLE SYSTEMS
GTIN	00077680195760
Manufacturers Part Number	1707B42T00
UPC	077680195760

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	Traditional Lightweight Type MC Cable With Ground And Neutral

Trade Size

Trade Size	10-2
------------	------

Packaging

Carton	250
Weight Per each	0.222

Uses, Certifications, and Standards

standard	UL 83, 1479, 1569, 1581, 2556 File Number E80042, UL File Number R-14141, NEC 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, Federal Specification A-A-59544 (Formerly J-C-30B), Meets OSHA And HUD Requirements, ISO 9001 Certified
Temperature Rating	194