



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MCT122SLBRGY250 MC 12/2 SL BR/Gy/GN 250'

Afc Cable

Catalog Number	MCT122SLBRGY250
Manufacturer	Afc Cable
Description	MC Cable, Solid, 600 V, 250 FT Overall Length, 0.495 In Outside Diameter, Copper Conductor Material, Thermoplastic Insulation Material, Brown, Gray and Green, 2 Conductors, +90 °C Operating Temperature, 0.147 LB/FT
Weight per unit	0.1470 (lbs/each)
Product Category	Teck

### Features

Conductor Size	12 AWG Conductor And Ground
Voltage Rating	600

### Material, Color, and Finish

Conductor Material	Solid Copper
--------------------	--------------

### Dimensions and Weight

Length	250 FT Coil
--------	-------------

### Descriptions

Description	MC 12/2 SL BR/GY/GN 250'
extra long description	AFC 1704B42T01 12-2 MC TUFF BN GY G
Special Features	Cable tray rated, install per NEC; May be surfaced mounted and embedded in plaster; Environmental air-handling space installation per NEC 300.22; UL Classified 1, 2, and 3 hour through (Fire) penetration product, R-14141; Made in USA of US and/or imported materials; ColorSpec ID system

### Manufacturer Information

Brand	AFC CABLE SYSTEMS
GTIN	00077680195357
UPC	077680195357

### Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	Traditional Lightweight Type MC Cable With Ground And Neutral

### Packaging

Carton	250
Weight	147
Weight Per each	0.147



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

standard

UL 83, 1479, 1569, 1581, 2556 File Number E80042, UL File  
Number R-14141, NEC 230.43, 300.22(C), 392, 396, 330, 501,  
502, 503, 530, 504, 505, 518, 520, 530, 645, Federal Specification  
A-A-59544 (Formerly J-C-30B), Meets OSHA And HUD  
Requirements, ISO 9001 Certified

Temperature Rating

90 Deg C (Dry)