



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MP300 Pxe MP300 Mobile Label Printer 1.5" W/ Acc *Panduit Corporation*

| | |
|------------------|--|
| Catalog Number | MP300 |
| Manufacturer | Panduit Corporation |
| Description | The Panduit MP300 Mobile Label Printer Is The Ideal Solution For Labeling In The Field. Our Printer Offers A Wide Variety Of Die-Cut and Continuous Label Sizes Up to 1.5" Wide and An Automatic Cutter With Capabilities For Full and Half Cuts. With 360 Dpi Resolution and Fast Printing Speed, The MP300 Increases Labeling Productivity. Printer Comes With One Label Cassette, Hard Carrying Case, Rechargeable Battery Pack, Magnetic Attachments, Usb Cable, and Power Adapter. Available Only In North America. |
| Weight per unit | 8.4 (lbs/each) |
| Product Category | Wiring Devices |

Features

| | |
|-------|-----|
| media | Yes |
|-------|-----|

Descriptions

| | |
|------------------------|--|
| Description | PXE MP300 MOBILE LABEL PRINTER 1.5" W/ ACC |
| extra long description | PAN MP300 PXE™ MP300 Mobile Label P |
| Long Description | The Panduit MP300 mobile label printer is the ideal solution for labeling in the field. Our printer offers a wide variety of die-cut and continuous label sizes up to 1.5" wide and an automatic cutter with capabilities for full and half cuts. With 360 dpi resolution and fast printing speed, the MP300 increases labeling productivity. Printer comes with one label cassette, hard carrying case, rechargeable battery pack, magnetic attachments, USB cable, and power adapter. Available only in North America. |
| Product Type | Pxe™ MP300 Mobile Label Printer, 1.5" Wide |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00613056763425 |
| Manufacturers Part Number | MP300 |
| UPC | 613056763425 |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 8.4 |