



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MPR400VBUXH0PA 400W or PS/MH ED37 Clear Bulb Mog Screw Base 4000K *Ge By Current Lamps*

Catalog Number	MPR400VBUXH0PA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 42000 LM Brightness (Lumens), 400 W, Clear, Hard Glass Material, 20000 H Average Life, EX39 Mogul Screw Base, M135/M155 Ansi Ballast Code, Non Dimmable, 4.62 In Diameter, 11.5 In Height, 41.5 % Mercury Content, 5.3 LB
Weight per unit	0.9300 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (EX39)
lumens	42000
Wattage	400

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	400W OR PS/MH ED37 CLEAR BULB MOG SCREW BASE 4000K
extra long description	GEL MPR400/VBU/XHOPA 46273 MULTIVAP
Special Features	11.5IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168462730
UPC	043168462730

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.93