



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## MVR400UED28 400W ED28 Metal Halide Reduced Glass Clear Mogul

*Ge By Current Lamps*

|                  |                                                                                                                                                                                                                                                                                                           |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | MVR400UED28                                                                                                                                                                                                                                                                                               |
| Manufacturer     | Ge By Current Lamps                                                                                                                                                                                                                                                                                       |
| Description      | Metal Halide Lamp, 65, 4000 K, 33100 LM (Horizontal);36000 LM (Vertical) Brightness (Lumens), 400 W, Clear, Hard Glass Material, 15000 H (Horizontal);20000 H (Vertical) Average Life, Mogul Base, M59 Ansi Ballast Code, Non Dimmable, 3.5 In Diameter, 8.25 In Height, 61.11 % Mercury Content, 5.92 LB |
| Weight per unit  | 0.4600 (lbs/each)                                                                                                                                                                                                                                                                                         |
| Product Category | Hid Quartz Metal Halide Lamps                                                                                                                                                                                                                                                                             |

### Features

|         |                   |
|---------|-------------------|
| Base    | Mogul Screw (E39) |
| Wattage | 400               |

### Material, Color, and Finish

|                             |                        |
|-----------------------------|------------------------|
| Color                       | Clear                  |
| color rendering index (cri) | 65                     |
| Style                       | Enclosed fixtures only |

### Descriptions

|                        |                                                  |
|------------------------|--------------------------------------------------|
| Description            | 400W ED28 METAL HALIDE REDUCED GLASS CLEAR MOGUL |
| extra long description | GEL MVR400/U/ED28 18904 MULTIVAPOR               |
| Special Features       | 8.25IN Length                                    |

### Manufacturer Information

|       |                      |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN  | 00043168189040       |
| UPC   | 043168189040         |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 0.46 |

### Uses, Certifications, and Standards

|             |                            |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|