


All Purpose Type Split Bolts - N-2/0SP



Drawn - SD

Approved - KM

Material - Copper / Finish: Tin Plated

Title - All Purpose Type Split Bolts



Max Run To Max Tap	2/0 - 2/0 Str AL CU
Min Run To Min Tap	1 - 8 Str AL CU
Max Run To Min Tap	2/0 - 8 Str AL CU
Min Equal Run - Tap	2 - 2 Str AL CU
4	Spacer Electrolytical Copper
3	Nut Bronze
2	Rider Bronze
1	Body Electrolytical Copper

