



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



NCG5050 1/2" NM Cord Grip

Crouse-Hinds

Catalog Number	NCG5050
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series NCG Cord Grip, Cable Range Min/Max: 0.20-0.50", Non-Armoured and Tray Cable, Non-Armoured Gland, Polyamide 6, General Purpose, 1/2" NPT
Weight per unit	0.0300 (lbs/each)
Product Category	Cable & Cord Grips

Features

dimensions	0.5000 IN X 0.5000 IN X 2.3800 IN
------------	-----------------------------------

Descriptions

Description	1/2" NM CORD GRIP
extra long description	MIDWEST NCG50 50 1/2 NON METALLIC C
Features	For use with portable cord, Crouse-Hinds series NCG and NCGB watertight cord grips terminate and protect conductors from mechanical damage due to vibration and movement. A neoprene bushing seals out oils, coolants, water, dust and other abusive agents. NCG and NCGB cord grips may be used with types S, SO, STO, SJ, SJT, SJTO and SVO portable cords. NCGS non-metallic cord grips are used in both commercial and residential grid-tied PV solar applications and are designed to accommodate the entry of multiple
Long Description	Eaton Crouse-Hinds series NCG cord grip, Cable range min/max: 0.20-0.50", Non-armoured and tray cable, Non-armoured gland, Polyamide 6, General purpose, 1/2" NPT
Product Type	1/2 Non Metallic Cord Grip

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564002440
Manufacturers Part Number	NCG50 50
UPC	784564002440

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cord grip

Packaging

Carton	1
Package	25
Weight Per each	0.03



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	NEMA 3 cULus Listed - UL File E23223
Temperature Rating	-25° to 40°C