

# NMLT125

## Straight Non-Metallic Connectors



Straight Non-Metallic Connector

Country of Origin: USA

Weight: 0.225 lbs/each

Height: 2.428"

Width: 2.428"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1-1/4"

Trade Size: 1-1/4"

### Packaging

Unit: 5 pcs

Standard: 25 pcs



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)

# NMLT125

## Straight Non-Metallic Connectors



Straight Non-Metallic Connector

Country of Origin: USA

Weight: 0.225 lbs/each

Height: 2.428"

Width: 2.428"

Material(s): UV-Rated Plastic

Conduit Type: Non-Metallic Liquid Tight Conduit, Type B Only

Knockout Size(s): 1-1/4"

Trade Size: 1-1/4"

### Packaging

Unit: 5 pcs

Standard: 25 pcs



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717  
Fax 570/562.0646  
[www.aifittings.com](http://www.aifittings.com)