



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## NMLT9075 3/4" Sealtight 90D NM Conn *Arlington Industries*

|                  |  |
|------------------|--|
| Catalog Number   | NMLT9075   |
| Manufacturer     | Arlington Industries   |
| Description      | Non-Metallic 90° Connector, 3/4 In Trade Size, Plastic, Gray, 2.55 In Length, 2.550 In Diameter, Threaded X Screw-In Connection, 3/4 In Knockout Size, 0.102 LB/Ea |
| Weight per unit  | 0.1000 (lbs/each)  |
| Product Category | Liquid Tight Fittings  |

### Features

|             |                     |
|-------------|---------------------|
| connection  | Threaded X Screw-In |
| Form        | Form B              |
| Material    | UV-Rated Plastic    |
| orientation | 90°                 |

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Gray |
|-------|------|

### Dimensions and Weight

|       |                                |
|-------|--------------------------------|
| Size  | L(2.840) x W(2.550) x H(2.550) |
| Width | 2.55                           |

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 3/4" SEALTIGHT 90D NM CONN          |
| extra long description | ARL NMLT9075 3/4"PVC LT 90 DEG CONN |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00018997549075 |
| UPC  | 018997549075   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | NON-METALLIC FITTINGS |
| Type                 | Push-In Connector     |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 10  |
| Package         | 50  |
| Weight Per each | 0.1 |

### Uses, Certifications, and Standards

|          |            |
|----------|------------|
| standard | UL and CSA |
|----------|------------|