



\*Quick Thread™ device hole



Nail-On

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
18.0	P-181	Single gang, angled mid-nails	2-5/8	2-5/16	3-3/4	24391	100	21
18.0	P-181QT	Single gang, angled mid-nails, Quick Thread™ device holes	2-5/8	2-5/16	3-3/4	24399	100	21
18.0	P-181RK	Single gang, reverse nails, molded-in Speed Klamps™	2-11/16	2-5/16	3-3/4	24398	100	21
20.5	P-201	Single gang, angled nails	3-1/16	2-5/16	3-3/4	24900	100	23
20.5	P-201QT	Single gang, angled nails, Quick Thread™ device holes	3-1/8	2-5/16	3-3/4	24909	100	25
20.5	P-201R	Single gang, reverse nails	3-1/16	2-5/16	3-3/4	24901	100	24
23.5	P-122SC	Patented single gang with side cube, angled mid-nails, four wire knockouts, 2 recessed buttons	1-3/4	2-9/32 (5-1/2 overall)	3-3/4	24914	24	9
24.0	P-241	Single gang, angled nails	3-9/16	2-5/16	3-3/4	24903	100	26
24.0	P-241QT	Single gang, angled nails, Quick Thread™ device holes	3-9/16	2-5/16	3-3/4	24904	100	27



Face Bracket Mount

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
18.0	P-181H	Single gang, face bracket mount, 1/2" NM knockouts	2-3/4	2-5/16	3-3/4	24916	48	10
18.0	P-181HZ	Single gang, face bracket mount, 1/2" NM knockouts, "Z" hanger	2-3/4	2-5/16	3-3/4	24919	36	11
24.0	P-241H	Single gang, face bracket mount	3-9/16	2-5/16	3-3/4	24907	50	12
24.0	P-241HQT	Single gang, face bracket mount, Quick Thread™ device holes	3-9/16	2-5/16	3-3/4	24908	50	12

Miscellaneous

Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
			D	W	H			
8.0	P-108E	Single gang, ears	1-1/4	2-5/16	3-3/4	24917	24	3
8.0	P-108H	Single gang, side bracket mount	1-1/4	2-5/16	3-3/4	24918	24	3
16.0	P-1160W	Single gang, ears, wing brackets, 1/2" NM knockouts	2-5/8	2-5/16	3-11/16	24915	48	10
18.0	P-1180W	Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout	3	2-1/4	3-11/16	92714	48	11
22.5	P-1220W	Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout	3-3/4	2-5/16	3-3/4	24913	48	14

All dimensions are in inches unless otherwise noted.

See page 32 for flexbox® Attachment Coding suffix descriptions.



Old Work/Manufactured Housing Boxes



Flush-Device Box

UL File No. E30594



\*Quick Thread™ device hole



Nail-On	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	18.0	P-181	Single gang, angled mid-nails	2-5/8	2-5/16	3-3/4	24391	100	21
	18.0	P-181QT	Single gang, angled mid-nails, Quick Thread™ device holes	2-5/8	2-5/16	3-3/4	24399	100	21
	18.0	P-181RK	Single gang, reverse nails, molded-in Speed Klamps™	2-11/16	2-5/16	3-3/4	24398	100	21
	20.5	P-201	Single gang, angled nails	3-1/16	2-5/16	3-3/4	24900	100	23
	20.5	P-201QT	Single gang, angled nails, Quick Thread™ device holes	3-1/8	2-5/16	3-3/4	24909	100	25
	20.5	P-201R	Single gang, reverse nails	3-1/16	2-5/16	3-3/4	24901	100	24
	23.5	P-122SC	Patented single gang with side cube, angled mid-nails, four wire knockouts, 2 recessed buttons	1-3/4	2-9/32 (5-1/2 overall)	3-3/4	24914	24	9
	24.0	P-241	Single gang, angled nails	3-9/16	2-5/16	3-3/4	24903	100	26
	24.0	P-241QT	Single gang, angled nails, Quick Thread™ device holes	3-9/16	2-5/16	3-3/4	24904	100	27



Face Bracket Mount	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	18.0	P-181H	Single gang, face bracket mount, 1/2" NM knockouts	2-3/4	2-5/16	3-3/4	24916	48	10
	18.0	P-181HZ	Single gang, face bracket mount, 1/2" NM knockouts, "Z" hanger	2-3/4	2-5/16	3-3/4	24919	36	11
	24.0	P-241H	Single gang, face bracket mount	3-9/16	2-5/16	3-3/4	24907	50	12
	24.0	P-241HQT	Single gang, face bracket mount, Quick Thread™ device holes	3-9/16	2-5/16	3-3/4	24908	50	12

Miscellaneous	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	8.0	P-108E	Single gang, ears	1-1/4	2-5/16	3-3/4	24917	24	3
	8.0	P-108H	Single gang, side bracket mount	1-1/4	2-5/16	3-3/4	24918	24	3
	16.0	P-1160W	Single gang, ears, wing brackets, 1/2" NM knockouts	2-5/8	2-5/16	3-11/16	24915	48	10
	18.0	P-1180W	Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout	3	2-1/4	3-11/16	92714	48	11
	22.5	P-1220W	Single gang, ears, wing brackets, molded-in Speed Klamps™, 1/2" NM knockout	3-3/4	2-5/16	3-3/4	24913	48	14

All dimensions are in inches unless otherwise noted.

See page 32 for flexbox® Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Flush-Device Box  
UL File No. E30594