



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## P4010ACSC0W CO/Smoke Detector

*Kidde Safety*

|                  |                                                                                                                                                                                                                                                              |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | P4010ACSC0W                                                                                                                                                                                                                                                  |
| Manufacturer     | Kidde Safety                                                                                                                                                                                                                                                 |
| Description      | Combination Smoke and Carbon Monoxide Alarm, Smoke and Carbon Monoxide Alarm, Battery Powered Type; Photoelectric/Electrochemical Operation Type; UL 217/2034, Nfpa 72 Approval; 85 Decibel At 10 Foot Horn Type; 120 Volt Ac 60 Hertz Voltage Rating/Source |
| Weight per unit  | 0.6000 (lbs/each)                                                                                                                                                                                                                                            |
| Product Category | Smoke & Heat Detectors                                                                                                                                                                                                                                       |

### Features

|                            |                               |
|----------------------------|-------------------------------|
| Horn Type                  | 85 Decibel at 10 Foot         |
| LED/Strobe Type            | Flashing LED                  |
| Number of Interconnections | 24 in                         |
| Operation Type             | Photoelectric/Electrochemical |
| Voltage Rating/Source      | 120 Volt AC 60 Hertz          |

### Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional Information | Overall Dimension 5.59 Inch Diameter x 1.91 Inch Depth; Battery Type 3 Volt Sealed-In Lithium; Relative Humidity Rating 10 to 95 Percent RH (Non-Condensing); Temperature Rating 40 to 100 Deg F                                                                                                                                                                                                                                                                                                                           |
| Commodity Description  | SMOKE & HEAT DETECTORS                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Description            | CO/SMOKE DETECTOR                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| extra long description | SMOKE AND CARBON MONOXIDE ALARM, WIRE-FREE TYPE; PHOTOELECTRIC, ELECTROMECHANICAL OPERATION TYPE; UL APPROVAL; 85 DECIBEL AT 10 FOOT HORN TYPE; 120 VOLT AC 60 HERTZ VOLTAGE RATING/SOURCE; GREEN LED INDICATING DEVICE WORKING, AMBER LED INDICATING ERROR, RED LED INDICATING DANGER DETECTED LED/STROBE TYPE; 24 INTERCONNECTION(S); BATTERY TYPE 3 VOLT SEALED LITHIUM; TEMPERATURE RATING 40 TO 100 DEG F; HUMIDITY RATING 10 TO 95 PERCENT RH NON-CONDENSING; OVERALL DIMENSION 5.59 INCH DIAMETER X 1.19 INCH DEPTH |
| Long Description       | COMBINATION SMOKE AND CARBON MONOXIDE ALARM, SMOKE AND CARBON MONOXIDE ALARM, BATTERY POWERED TYPE; PHOTOELECTRIC/ELECTROCHEMICAL OPERATION TYPE; UL 217/2034, NFPA 72 APPROVAL; 85 DECIBEL AT 10 FOOT HORN TYPE; 120 VOLT AC 60 HERTZ VOLTAGE RATING/SOURCE                                                                                                                                                                                                                                                               |
| Product Type           | Combination Smoke and Carbon Monoxide Alarm                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Kidde          |
| GTIN                      | 00047871273232 |
| Manufacturers Part Number | 21027323       |
| UPC                       | 047871273232   |

## Taxonomies, Classifications, and Categories

|      |                                                  |
|------|--------------------------------------------------|
| Type | Smoke and Carbon Monoxide Alarm, Battery Powered |
|------|--------------------------------------------------|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.6 |

## Uses, Certifications, and Standards

|          |                      |
|----------|----------------------|
| Approval | UL 217/2034, NFPA 72 |
|----------|----------------------|