

Specifications



Photo is representative



Eaton P48G11S05P

Eaton Mini-Power Center, Single-phase, PV:
480V, Taps: 2 at -5% FCBN, SV: 120/240V,
115°C, 5 kVA, Al windings , Indoor-
Outdoor.B45, Frame: 284

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S05P
UPC	786680140204
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	16 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	146 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed IEEE Certified CSA Certified ANSI

Physical Attributes

COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 3R
FRAME	284
TAP SIZE	2 at -5% FCBN
TYPE	Mini-power center
WIRING CONNECTION	110A5K

Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

Performance Ratings

FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	120/240 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	5 kVA

Resources

CATALOGS	Commercial Distribution Transformers, Volume 2, Tab 2
MULTIMEDIA	Eaton's Transformer Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - P48G11S05P

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton P48G11S05P

Eaton Mini-Power Center, Single-phase, PV:
480V, Taps: 2 at -5% FCBN, SV: 120/240V,
115°C, 5 kVA, Al windings , Indoor-
Outdoor.B45, Frame: 284

General specifications

PRODUCT NAME	Eaton Mini-Power center
CATALOG NUMBER	P48G11S05P
UPC	786680140204
PRODUCT LENGTH/DEPTH	8.9 in
PRODUCT HEIGHT	16 in
PRODUCT WIDTH	11.9 in
PRODUCT WEIGHT	146 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	NEMA Compliant
CERTIFICATIONS	UL Listed IEEE Certified CSA Certified ANSI

Physical Attributes		Performance Ratings	
COIL MATERIAL	Aluminum	FREQUENCY RATING	60 Hz
ENCLOSURE	NEMA 3R	PHASE	Single-phase
FRAME	284	PRIMARY VOLTAGE	480 V
TAP SIZE	2 at -5% FCBN	SECONDARY VOLTAGE	120/240 V
TYPE	Mini-power center	TEMPERATURE RISE	115 °C rise
WIRING CONNECTION	110A5K	VOLT AMPERE RATING	5 kVA

Miscellaneous		Resources	
WEATHERSHIELD	Indoor-Outdoor	CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
		MULTIMEDIA	Eaton's Transformer Flex Center
		SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - P48G11S05P

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

