

Eaton P48G11S1020

Catalog Number: P48G11S1020

10 KVA Mini Power Center 1PH 480V-120/240V 20 spaces



General specifications

Product Name

Eaton Mini-Power center

Catalog Number

P48G11S1020

UPC

786680225550

Product Length/Depth

11.6 in

Product Height

23.25 in

Product Width

13.1 in

Product Weight

275 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

NAFTA

Certifications

ANSI

CSA Certified

UL Listed

IEEE Certified



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 3R

Frame

286

Insulation

180 °C

Mounting

Wall Mount

Tap size

2 at -5% FCBN

Type

Mini-power center

Wiring connection

M48G11G

Performance Ratings

Frequency rating

60 Hz

kVA

10 kVA

Kva Rating

10 kVA

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

10 kVA

Miscellaneous

Modification 1

NEMA 3R

Weathershield

Not required

Resources

Multimedia

[Eaton's Transformer Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - P48G11S1020](#)