ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



PB30 Power Inlet Box, 30A, 120/240V, L14-

Reliance Controls Corp.

Catalog Number	PB30
Manufacturer	Reliance Controls Corp.
Description	Power Inlet Box, 30A, 120/240V, L14-30P
Weight per unit	N/A
Product Category	Gen Purpose Switches

Descriptions

Description	POWER INLET BOX, 30A, 120/240V, L14-
extra long description	RAINTIGHT TYPE; POWDER COATED STEEL MATERIAL; L14-30P CONFIGURATION; UL (CANADA AND US) APPROVAL; 125/250 VAC VOLTAGE RATING; 30 AMPERE CURRENT RATING; SPRING LOADED WEATHERPROOF COVER TYPE; GROUNDING; OVERALL DIMENSION 4 INCH W X 2.63 INCH D X 6 INCH H; GENERATOR INPUT RUNNING RATE 7500 W; WIRING SPACE 100 CU INCH; NEMA RATING 3R; APPLICATION INDOOR/OUTDOOR; INCLUDES CIRCUIT BREAKER
Long Description	POWER INLET BOX, 30A, 120/240V, L14-30P
Product Type	Transfer Switch Power Inlet Box

Manufacturer Information

Brand	Reliance Controls Corp.
Manufacturers Part Number	PB30

Taxonomies, Classifications, and Categories

Category Description	WEATHERPROOF BOXES & COVERS

Packaging

Carton	1
Weight Per each	0