

Specifications

Photo is representative

Eaton PDG13M0070MSAJ

Eaton Power Defense motor circuit protector, Globally Rated, Frame 1 Motor Circuit Protector, Three Pole, 70A, 65kA/480V, Adjustable Instantaneous Standard Calibrations, Standard Line and Load

General specifications

PRODUCT NAME	Eaton Power Defense motor circuit protector
CATALOG NUMBER	PDG13M0070MSAJ
UPC	786679318089
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	139.7 mm
PRODUCT WIDTH	76.2 mm
PRODUCT WEIGHT	1.36 kg
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 489 CSA IEC 60947-2 CCC Marked

Delivery program

AMPERAGE RATING	70A
FRAME	1
NUMBER OF POLES	Three-pole

Technical data - Electrical

VOLTAGE RATING	600 Vac
-----------------------	---------

Technical data - Mechanical - Terminals

TERMINALS	Standard Line and Load
------------------	------------------------

General information

CIRCUIT BREAKER TYPE	PD1 Global
CLASS	Class A

Technical data - Mechanical

SWITCH OFF TECHNIQUE	Thermomagnetic
-----------------------------	----------------

Technical information

INTERRUPT RATING	65 kAIC at 480 Vac
	65 kAIC at 480 V (UL) 100 kAIC at 240 V (UL) 70 kAIC Icu/50 kAIC Ics/154 kAIC Icm at 380-415 V (IEC)
INTERRUPT RATING RANGE	35 kAIC Icu at 250 Vdc 100 kAIC Icu/100 kAIC Ics/220 kAIC Icm at 240 V (IEC) 35 kAIC Icu at 125 Vdc 25 kAIC at 600 V (UL/CSA)

Resources

3D CAD DRAWING PACKAGE

[Eaton Power Defense MCCB PDG13M0070MSAJ 3D drawing](#)

APPLICATION NOTES

[Consulting application guide - molded case circuit breakers](#)

BROCHURES

[Power Defense molded case circuit breaker selection poster](#)

[Power Defense technical selling booklet](#)

[Power Defense brochure](#)

[Power Defense molded case circuit breakers - Frame 1 product aid](#)

CATALOGS

[Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2](#)

CERTIFICATION REPORTS

[Power Defense Declaration concerning California's Proposition 65](#)

[PDG1 CSA certification](#)

[PDG1 CCC certification](#)

[EU Declaration of Conformity - Power Defense molded case circuit breakers](#)

[PDG1 UL authorization](#)

INSTALLATION INSTRUCTIONS

[Power Defense Frame 1 UL global interphase barrier instructions - IL012313EN](#)

[Power Defense Frame 1 UL global tunnel terminal \(aluminum\) 125A 3P - IL012166EN H03](#)

[Power Defense Frame 1 UL global Padlockable Handle Lock Hasp - IL012225EN](#)

[Power Defense Frame 1 UL global DIN rail adapter metal three pole - IL012187EN](#)

[Power Defense Frame 1](#)
[UL global terminal shield](#)
[cover IP30 3P -](#)
[IL012174EN](#)

[Power Defense Frame 1-2-](#)
[3-4 IP door barrier](#)
[assembly instructions -](#)
[IL012278EN](#)

[Power Defense Frame 1](#)
[UL global screw terminal](#)
[end cap kit metric 125A 3P](#)
[- IL012171EN](#)

[Power Defense Frame 1](#)
[UL global DIN rail adapter](#)
[2, 3, 4-pole - IL012185EN](#)

[Power Defense Frame 1](#)
[UL global DIN rail adapter](#)
[three or four pole -](#)
[IL012186EN](#)

[Power Defense Frame 1](#)
[UL global screw terminal](#)
[end cap kit 125A 3P -](#)
[IL012163EN](#)

[Power Defense Frame 1](#)
[Instructions - IL012152EN](#)

[Power Defense Frame 1](#)
[UL global handle block](#)
[non padlockable -](#)
[IL012177EN](#)

[Power Defense Frame 1](#)
[UL global lock padlockable](#)
[handle hasp IL012180EN](#)

[Power Defense Frame 1](#)
[UL global handle block](#)
[padlockable - IL012178EN](#)

[Power Defense Frame 1](#)
[UL Global variable depth](#)
[rotary handle mech](#)
[installation instructions -](#)
[IL012308EN](#)

[Power Defense](#)
[padlockable handle lock](#)
[hasp top off only](#)
[installation instructions -](#)
[IL012226EN](#)

	Power Defense Frame 1 UL global box terminal (steel) 125A 3P - IL012165EN H03 Power Defense Frame 1 UL global interphase barrier - IL012176EN Power Defense Frame 1 UL global handle block padlockable off only - IL012179EN
INSTALLATION VIDEOS	Power Defense Frame 1 UL Global Aux, Alarm, ST and UVR Animated Instructions.rh
MULTIMEDIA	Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video Power Defense Breakers Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video Power Defense Frame 5 Trip Unit How-To Video Eaton Power Defense for superior arc flash safety Power Defense Frame 1 Aux, Alarm, and Shunt Trip How-To Video Power Defense molded case circuit breakers Power Defense Frame 6 Trip Unit How-To Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PDG13M0070MSA]
TIME/CURRENT CURVES	Power Defense time current curve Frame 1 - PDG1 Power Defense time current curves MCP Motor Circuit Protection – PD1, PD2, PD3
WHITE PAPERS	Single and double break MCCB performance revisited

[Molded case and low-voltage breaker health](#)

[Safer by design: arc energy reduction techniques](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

