

Specifications

Photo is representative

Eaton PDG23G0040TFFL

Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 2, Three Pole, 40A, 35kA/480V, T-M (Fxd-Fxd) TU, Standard Terminals Load Only (PDG2X3T100)

General specifications

PRODUCT NAME	Eaton Power Defense molded case circuit breaker
CATALOG NUMBER	PDG23G0040TFFL
UPC	786679911020
PRODUCT LENGTH/DEPTH	88.9 mm
PRODUCT HEIGHT	152.4 mm
PRODUCT WIDTH	104.6 mm
PRODUCT WEIGHT	1.82 kg
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC 60947-2 CCC Marked CSA UL 489

Delivery program

AMPERAGE RATING	40 A
CIRCUIT BREAKER FRAME TYPE	Complete breaker
FRAME	2
NUMBER OF POLES	Three-pole

Technical data - Electrical

VOLTAGE RATING	600 Vac
-----------------------	---------

Technical information

INTERRUPT RATING	35 kAIC at 480 Vac
INTERRUPT RATING RANGE	8 kAIC Icu/ 4 kAIC Ics/ 16.8 kAIC Icm @690V (IEC) 20 kAIC Icu/ 15/13 kAIC Ics/ 42 kAIC Icm @525V South Africa (IEC) 10 kAIC Icu @250 Vdc 18 kAIC @600V (UL/CSA) 35 kAIC @480V (UL) 65 kAIC @240V (UL) 36 kAIC Icu/ 36 kAIC Ics/ 75.6 kAIC Icm @380-415V (IEC) 10 kAIC Icu @125 Vdc 25 kAIC Icu/ 20 kAIC Ics/ 52.5 kAIC Icm @480V Brazil (IEC) 30 kAIC Icu/ 22.5 kAIC Ics/ 63 kAIC Icm @440V (IEC) 55 kAIC Icu/ 55 kAIC Ics/ 121 kAIC Icm @240V (IEC)

General information

CIRCUIT BREAKER TYPE	PD2 Global
CLASS	Class A
TRIP TYPE	T298

Technical data - Mechanical - Terminals

TERMINALS	Standard Terminals Load Only
------------------	------------------------------

Resources

3D CAD DRAWING PACKAGE	Eaton Power Defense PDG23G0040TFFL 3D drawing
APPLICATION NOTES	Consulting application guide - molded case circuit breakers Power Defense molded case circuit breaker selection poster Power Defense brochure Power Defense technical selling booklet Power Defense molded case circuit breakers - Frame 2 product aid
CATALOGS	Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2 Power Defense Declaration concerning California's Proposition 65 PDG4 CB report
CERTIFICATION REPORTS	EU Declaration of Conformity - Power Defense molded case circuit breakers PDG4 CCC certification PDG2 CB report

**INSTALLATION
INSTRUCTIONS**

[Power Defense Frame 2
box terminal \(aluminum\),
225A, 3 pole instructions -
IL012235EN H03](#)

[Power Defense Frame 2
PDG2 and PDC\(E\)9 breaker
instructions - IL012106EN](#)

[Power Defense Frame 2
Direct Rotary Handle Assy
With Interlock Version
Instructions
\(IL012138EN\).pdf](#)

[Power Defense Frame 2
multi wire connector kit -
PDG2X3\(2\)\(4\)TA2253W
instructions - IL012243EN
H01](#)

[Power Defense Frame 2
handle mech variable
depth rotary handle
instructions - IL012136EN](#)

[Power Defense Frame 2
box terminal \(steel\), 100A,
3 pole instructions -
IL012234EN H03](#)

[Power Defense Frame 2
handle mech direct rotary
handle instructions -
IL012134EN](#)

[Power Defense Frame 1-2-
3-4 IP door barrier
assembly instructions -
IL012278EN](#)

[Power Defense Frame 2
global terminal shield, 3
pole - IL012330EN](#)

[Power Defense Frame 2
tunnel terminal kits -
PDG2X1TA225K
instructions- IL012239EN
H01](#)

[Power Defense Frame 2
tunnel terminal
\(aluminum\), 150A, 3 pole
instructions - IL012238EN
H03](#)

[Power Defense Frame 2
locking devices and handle
block instructions -
IL012149EN](#)

[Power Defense Frame 2
shunt trip UVR instructions
- IL012130EN](#)

[Power Defense Frame
2/3/4/5/6 voltage neutral
sensor module wiring
instructions – IL012316EN](#)

[Power Defense Frame 2
tunnel terminal
\(aluminum\), 100A, 3 pole
instructions - IL012237EN
H03](#)

[Power Defense Frame 2
clamp terminal \(steel\),
20A, 3 pole instructions -
IL012246EN H03](#)

[Power Defense Frame 2
terminal kit -
PDG2X3\(2\)\(4\)TA225RF
instructions - IL012245EN
H01](#)

[Power Defense Frame 2
screw terminal end cap
kit, 225A, 3 pole
instructions - IL012258EN
H01](#)

[Power Defense Frame 2
terminal kit -
PDG2X3\(2\)\(4\)TA150RF
instructions - IL012244EN
H01](#)

[Power Defense Frame 1
IEC and Frame 2 Rotary
Mechanism with NFPA
Handle Attachment
Instructions
\(IL012260EN\).pdf](#)

[Power Defense Frame 2
tunnel terminal
\(aluminum\), 50A, 3 pole
instructions - IL012236EN
H03](#)

	Power Defense Frame 2 multi wire connector kit - PDG2X3(2)(4)TA2256W instructions - IL012242EN H01
	Power Defense Frame 2 withTMTU, Shunt Trip UVR Animated Instructions.rh
	Power Defense Frame 2 TMTU Aux, Alarm, ST and UVR Animated Instructions.rh
INSTALLATION VIDEOS	Power Defense Frame 2 Locking Devices and Handle Block Animated Instructions.pdf.rh
	Power Defense Frame 2 Handle Mech Variable Depth Rotary Handle Animated Instructions.rh
	Power Defense Frame 2 Bell Alarm with PXR Animated Instructions.pdf.rh
	Power Defense Frame 2 Aux, Alarm, Shunt Trip, and UVR How-To Video
	Power Defense Frame 2 Direct Rotary Handle Mechanism Installation How-To Video
	Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video
MULTIMEDIA	Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video
	Power Defense Breakers
	Power Defense Frame 6 Trip Unit How-To Video
	Eaton Power Defense for superior arc flash safety
	Power Defense Frame 5 Trip Unit How-To Video

	Power Defense molded case circuit breakers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PDG23G0040TFFL
TIME/CURRENT CURVES	Power Defense time current curve Frame 2 - PD2
	Single and double break MCCB performance revisited
	Intelligent circuit protection yields space savings
WHITE PAPERS	Making a better machine
	Molded case and low-voltage power circuit breaker health
	Molded case and low-voltage breaker health
	Safer by design: arc energy reduction techniques

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

